



PUMPS/DISPENSERS & COLD HOLDING BAR & RAIL ACCESSORIES

Date:

Project:

Quantity:

Item Number:



NSF

Standard Fountain Jars

Plastic
Deep 82557
Shallow 82558



NSF

82559

82545

80310

Lids



NSF

HOLDCOLD™ Fountain Jars

Individual Set of 1 each
Black 82632 Set 82634
White 82633



NSF

82561
82562

Ladles



NSF

94141

Eutectic Ice Pack

Standard Fountain Jars

Plastic fountain jars are constructed of high-impact Polypropylene. Similar to the stainless steel jars above, the plastic fountain jars are notched. They also have (3) exclusive features: rear tabs with holes to allow Sanitary Hinged Lid (82545) to attach to the jar, molded feet to prevent tipping, and side slots for use with Hinged Lid (80310).

Standard Fountain Jar Specifications

Model		Height	Width	Depth	Capacity
82558	in	6 ⁵ / ₈	4 ¹ / ₈	6 ⁷ / ₈	2 qt
	cm	16.8	10.5	17.5	1.9 L
82557	in	9 ¹ / ₈	4 ¹ / ₈	6 ⁷ / ₈	3 ¹ / ₂ qt
	cm	23.2	10.5	17.5	3.3 L

Hole Opening: 4 ⁵/₁₆ x 7 in (11 x 17.8 cm) on all jars

HOLDCOLD™ Fountain Jars

HOLDCOLD™ jars are constructed of durable ABS plastic and filled with a non-toxic refrigerant gel. Each jar is notched to allow the lid to close over a ladle for increased sanitation. They also have molded feet to prevent tipping. Place jar in the freezer for eight hours prior to use. HOLDCOLD™ Jars will maintain product temperature for up to (12) hours, when placed in an insulated unit and filled with refrigerated product.

HOLDCOLD™ Fountain Jar Specifications

Models		Height	Width	Depth	Capacity
82632 & 82633	in	9 ⁵ / ₈	4 ¹ / ₈	6 ⁷ / ₈	2 ¹ / ₄ qt
	cm	24.4	10.5	17.5	2.1 L

Ladles

Both our long (10", 25.4 cm) (82561) and short (7", 17.8 cm) (82562) ladles are constructed of stainless steel. Each has a 1 ounce (30 mL) capacity.

Lids

Models 82559 and 82545 are constructed of stainless steel with a polished finish. Our hinged lid, 80310 is constructed of impact and scratch-resistant clear plastic. Stainless steel and plastic fountain jars can use a Lift-Off Lid (82559). Plastic jars also accept Hinged Lid 80310 or Sanitary Hinged Lid 82545.

HOLDCOLD™ deep jars can use Lift-Off Lid (82559).

Lid Usage

Model & Description	Plastic	Stainless	HOLDCOLD™
82559 Lift-Off	Yes	Yes	Yes
80310 Hinged	Yes	No	No
82545 San. Hinged	Yes	No	No

Eutectic Ice Pack

Constructed of a high-density Polyethylene shell, the Eutectic Ice Pack is for use in the insulated Serving Bar. Tests show a temperature gain of just two degrees over a (6) hour period. Use one ice pack per jar for more efficient cooling than ice without the mess.

Eutectic Ice Pack Specifications

Model		Height	Width	Depth
94141	in	6	4	1
	cm	15.2	10.2	2.5

CAD Library

Individual CAD images can be downloaded from product pages on our web site. We are also a member of The KCL CADalog with more than 100 other manufacturers. Our complete collection of CAD files can be purchased through Kochman Consultants, Ltd. at kclcad.com.

Warranty

Server Products equipment is backed by a two-year limited warranty against defects in materials and workmanship. For our complete warranty statement, see our web site or contact us.





Make your own combination. Select a base from a Bar or Rail Combination sheet then choose from the accessories listed below.

Standard Fountain Jars

- 82557 Deep, Polypropylene
- 82558 Shallow, Polypropylene

HOLDCOLD™ Fountain Jars

For use with insulated Serving Bars.

- 82632 Deep, Black HOLDCOLD™
- 82633 Deep, White HOLDCOLD™
- 82634 Set of 1 Black & 1 White HOLDCOLD™

Condiment Pumps – Stainless Steel

For details, see Fountain Jar Dispensers sheet 02047.

- CP-F 83330 (fits deep jar)
- CP-200 83300 (fits shallow jar)

Fountain Pumps – Stainless Steel

For details, see Fountain Jar Dispenser sheet 02009.

- FP-V 82120 (fits deep jar)
- FPV-DI 82520 (fits deep jar)

Note: Colored, engraved knobs to identify flavors are available for stainless steel pumps and lids.

Solution™ Pumps – Plastic

For details, see Server Solution™ sheet 02061.

- PS-F 81910 (fits deep jar)
- PS-200 84060 (fits shallow jar)

Lids

For use with plastic fountain jar.

- 82559 Lift-Off
- 83800 Hinged (attaches to jar)
- 82545 Sanitary Hinged (attaches to jar)

Lids

For use with stainless steel fountain jar.

- 82559 Lift-Off
- 82595 Lid and attached ladle (shallow jar only)

Lid

For use with HOLDCOLD™ fountain jar.

- 82559 Lift-Off

Ladles

- 82561 10", 25.4 cm (for deep jar)
- 82562 7", 17.8 cm (for shallow jar)

Other Accessories

- 94141 Eutectic Ice Pack—Rectangular
Use in insulated Serving Bars (one per jar)

FOB Richfield, Wisconsin 53076

All models listed 



